



## 32-bit MCU with Arm® Cortex®-M Core **RENESAS RA FAMILY**

### **Delivering the Ultimate Promise of IoT with Software Flexibility**

The Renesas RA Family is a new 32-bit MCU family built on the Arm® Cortex®-M core architecture. Offering a wide range of performance and features, the Renesas RA Family meet the scalability, power consumption and performance needs of nearly any embedded systems end-product.





### **Strong Security**

- Leading-edge, integrated Renesas Security IP
- An extra layer of embedded hardware security providing tamper detection and resistance to side-channel attacks
- Integrated Arm® v8-M TrustZone®



### Flexible Software Solution

- Supported by an open and flexible ecosystem concept, the Flexible Software Package (FSP)
- Can be replaced and expanded by any other RTOS or middleware



- Arm Cortex-M23 core for the most cost/power sensitive applications
- Arm Cortex-M4/M33 cores to deliver the best balance of performance and power
- Arm Cortex-M85 core with Helium<sup>™</sup> technology for unprecedented performance



### 💢 Best-in-Class Peripheral IP

- Excellent HMI capacitive touch technology
- The industry's highest code flash memory capacity
- Wide range of connectivity solutions

### Renesas RA Product Series

The four Renesas RA Family MCU series are based on 32-bit Arm® Cortex®-M cores. All four Renesas RA Series have been designed on common DNA, making these products feature- and pin-compatible. This allows easy scalability and code reuse from one device to another.

RA6  1.68-3.6V  Connectivity, Security, Analog  up to 2MB Flash, 2MB SRAM  Al/ML, HMI  RA6  Up to 240MHz 2.7-3.6V  Advanced Performance, Connectivity, Security  Up to 100MHz 1.6V-5.5V  Excellent Power, High Performance Mix Paired with Security  Up to 1MB Flash, 128kB SRAM  Al/ML, HMI  Motor/Inverte up to 1MB Flash, 128kB SRAM  Motor/Inverte Sensor, Wireles	High Performance	Performance Range	Feature	Series Memory Ranges	ASSP Extensions
RA4  Up to 100MHz 1.6V-5.5V  Connectivity, Security  up to 2MB Flash, 640kB SRAM  Al/ML, HMI  Medium Memory Integration: up to 1MB Flash,128kB SRAM  Motor/Inverte Sensor, Wireles	RA8	0.00. = .0			Motor/Inverter AI/ML, HMI
1.6V-5.5V Mix Paired with Security up to 1MB Flash,128kB SRAM Sensor, Wireless	RA6	'		, ,	Motor/Inverter AI/ML, HMI
Madium mamani internation	RA4	'	9		Motor/Inverter Sensor, Wireless
Low Power Low Power up to 256kB Flash, 32kB SRAM Rich Analog	RA2	Up to 60MHz 1.6V-5.5V	Low Power	Medium memory integration: up to 256kB Flash, 32kB SRAM	Rich Analog

renesas.com 2023.10

### Target Markets and Benefits

# **Industrial Automation**

- Long product life
- Temperature up to 105°C
- Industrial quality grade
- Strongest robustness
- 24-bit ∑△ ADC for sensors

### Security

- Isolated crypto subsystem
- Symmetric/asymmetric hardware acceleration
- True Random Number Generator (TRNG)
- NIST-certified algorithms
- Key isolation and management

### Connectivity



- CAN/USB/Ethernet
- Large amount on serial interfaces
- QSPI interfaces
- Integrated crypto module

- Wide range of connectivity
- Rich analog features

### Metering

- Scalable lineup
- Industrial quality grade
- Long product life
- Integrated crypto module

### Whitegoods



- Scalable lineup
- Motor control solutions
- Capacitive touch interface
- LCD control



#### ■ High Flash/RAM ratio

- Small packages

### **Tools and Support**

IDE	Renesas e²studio	Keil MDK	IAR EWARM
Compiler	• GCC • LLVM • Arm Compiler * • IAR Arm Compiler *	Arm Compiler *	• IAR Arm Compiler *
Debugger	• Renesas E2 / E2 Lite • SEGGER J-Link	• SEGGER J-Link • Keil ULINK / CMSIS-DAP (limited support)	• SEGGER J-Link • IAR I-jet • Renesas E2 / E2 Lite • CMSIS-DAP (limited support)

<sup>\*:</sup> Compiler must be purchased and licensed directly from 3rd-party

## Code generation & auto code complete & IDE updates **Build with Partner compilers**

#### **Evaluation Kit**

- Full MCU evaluation including on-board debugger
- Individual kits for several products of each Renesas RA Series are available
- Board ecosystem compatibility and remarkable ease of use



For more information about the Renesas RA MCU family, visit: www.renesas.com/RA

#### renesas.com

#### Corporate Headquarters

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/

© 2023 Renesas Electronics Corporation. All rights reserved.

